





Anti-Snagging Slider Cover

Item Specification



This item cannot be used for products intended for infants/children under the age of 3.




Size	Chain	Class	Slider	
			OK	NG
05	Coil	OR/OL MR/ML	DA(B), ZA(B), CA(B), DF(B), NA(B), DW, DX	DS, DU

- Regarding other available sliders, please contact your sales person.

- Applicable only to pulls with a width of 13mm or below.
- Not applicable to AquaGuard® water repellent chain or chain with reflective films, as the surface is subject to harsher abrasion with the slider cover.


Instructions for sewing




- Please sew at least 5mm (6-7mm if the material is uneven in thickness) away from elements to prevent it from snagging.

Instructions for Use

① Attaching the top cover to the front side of the slider




Place the **slider pull** through the larger hole of the top cover.





Adjust the position of the top cover to align with the **slider body** and chain with the smaller hole placed just over the slider body.

② Attaching the bottom cover to the back side of the slider



The bottom cover has two prongs sticking up. Turn over the zipper.



Place the prongs into the back side of the smaller hole on the top cover.

③ Snap the prongs together for engagement



Snap the prongs into the smaller hole on the backside of the top cover.

You may use an apparatus such as a small plier to apply force until both covers are firmly engaged.


④ Checking



Please check to make sure there is no gap between the two parts.

Others

Front



Reverse



When attaching the parts to slider for reverse coil zippers, top/bottom covers are to be switched and used upsidedown.

Two-way



Covers are available to be used on the sliders with double-sided pulls such as DW (without locking function).

⚠ Please do not separate the parts once engaged or breakage may result.

